

TECHNICAL DATA SHEET

Part No. 166-90221
Article No. 166-90221
Type PSR0500



A lightweight tubing with a smooth inside bore, made of a spiral reinforced PVC material that provides high flexibility. This tubing is well-suited for protecting wire and cable bundles in extremely tight spaces. UV resistant. Use with HelaGuard Non-Metallic Compression Fittings to create an enclosed system.

Material	Polyvinylchloride (PVC)
Operating Temperature	-4°F to +158°F (-20°C to +70°C)
Flammability	EN IEC 61386
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	12
Customs Number	3926909988

Inner Diameter (imperial)	0.63 "
Inner Diameter 2 (metric)	16 mm
Inside Bend Radius (imperial)	1.38 "
Inside Bend Radius (metric)	35 mm
Length (imperial)	100.0 ft
Length (metric)	30.5 m
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	20 mm
Outside Diameter (imperial)	0.83 "
Outside Diameter (metric)	21.0 mm

