

TECHNICAL DATA SHEET

Part No. 166-90288
Article No. 166-90288
Type HG-SW0310



A standard weight corrugated conduit made of PA6 nylon that offers flexible abrasion protection for wire and cable bundles. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	164.04 ft
Carton Qty.	100
Customs Number	3926909988

Inner Diameter (imperial)	0.39 "
Inner Diameter 2 (metric)	9.8 mm
Inside Bend Radius (imperial)	0.99 "
Inside Bend Radius (metric)	25 mm
Length (imperial)	164.0 ft
Length (metric)	50.0 m
Nominal Diameter (imperial)	0.31 "
Nominal Diameter (metric)	13 mm
Outside Diameter (imperial)	0.51 "
Outside Diameter (metric)	13.0 mm

