

TECHNICAL DATA SHEET

Part No. 166-90293
Article No. 166-90293
Type HG-SW1250



A standard weight corrugated conduit made of PA6 nylon that offers flexible abrasion protection for wire and cable bundles. Easy to cut and use, the material is highly resistant to solvents and oils. Combine with HelaGuard non-metallic fittings for IP66 rating or greater protection against water, wind and dirt.

Inner Diameter 2 (metric)	35.5 mm
Length (imperial)	82.0 ft
Length (metric)	25.0 m
Nominal Diameter (metric)	42 mm
Outside Diameter (metric)	42.5 mm

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	82.0 ft
Carton Qty.	14
Customs Number	3926909988

RoHS✓