

TECHNICAL DATA SHEET

Part No. 166-90326
Article No. 166-90326
Type HG075-S-M25



HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use

Length (imperial)	1.97 "
Length (metric)	50 mm
Nominal Diameter (imperial)	0.75 "
Nominal Diameter (metric)	28 mm
Pkg. Qty.	10

RoHS✓