

TECHNICAL DATA SHEET

Part No. 166-90359
Article No. 166-90359
Type ALNPB-1500



Locknuts work with metric threaded fittings or knockout entries.

Material	Nickel Plated Brass (NPB)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use

Description	HelaGuard Metallic Locknuts, 1.5" NPT Thread
Pkg. Qty.	4