

TECHNICAL DATA SHEET



Part No. 166-90467
Article No. 166-90467
Type ALNPB-2000



Locknuts work with metric threaded fittings or knockout entries.

Material	Nickel Plated Brass (NPB)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
UV Resistant	No
Use Conditions	For Indoor Use Only

Description	HelaGuard Metallic Locknuts, 2" NPT Thread, 2" Dia
Pkg. Qty.	2