TECHNICAL DATA SHEET

HellermannTyton

Part No. 166-90799
Article No. 166-90799
Type HGU42-S-M40B



Straight Snap-On style Metric or NPT threaded nylon fittings provide a true one-piece component solution; seals and locknuts are included. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids, and solvents. Designed for easy removal with a small screwdriver. UL-Listed fittings deliver IP66 + IP67 + IP68 + IP69 ingress protection.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Halogen Free	Yes
IP-Rating	IP68
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	2
Carton Qty.	1
Customs Number	3926909988

Length (imperial)	2.40 "
Length (metric)	61.0 mm
Nominal Diameter (imperial)	1.25 "
Nominal Diameter (metric)	42 mm
Outside Diameter (imperial)	2.36 "
Outside Diameter (metric)	60.0 mm

HF RoHS

c UL us

created on 2026-04-15