# TECHNICAL DATA SHEET

HellermannTyton

**Part No.** 166-90824
**Article No.** 166-90824
**Type** HGU16-90M-M16B



Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.

| | |
|---|---|
| **Material** | Nickel Plated Brass (NPB), Polyamide 6.6 (PA66) |
| **Operating Temperature** | -58°F to +275°F (-50°C to +135°C) |
| **Halogen Free** | Yes |
| **IP-Rating** | IP68 |
| **UV Resistant** | No |
| **Use Conditions** | For Indoor and Outdoor Use |

| | |
|---|---|
| **Length (imperial)** | 2.44 " |
| **Length (metric)** | 62 mm |
| **Nominal Diameter (imperial)** | 0.38 " |
| **Nominal Diameter (metric)** | 16 mm |
| **Pkg. Qty.** | 10 |

HF ✓ RoHS ✓