

TECHNICAL DATA SHEET

Part No. 166-90851
Article No. 166-90851
Type HGU34-S-M40B



Straight Snap-On style Metric or NPT threaded nylon fittings provide a true one-piece component solution; seals and locknuts are included. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids, and solvents. Designed for easy removal with a small screwdriver. UL-Listed fittings deliver IP66 + IP67 + IP68 + IP69 ingress protection.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Halogen Free	Yes
IP-Rating	IP68
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	1
Customs Number	3926909988

Length (imperial)	2.09 "
Length (metric)	53.0 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	34 mm
Outside Diameter (imperial)	1.93 "
Outside Diameter (metric)	49.0 mm

