

TECHNICAL DATA SHEET

Part No. 166-90984
Article No. 166-90984
Type HG-DC0500



A standard-weight, polypropylene, corrugated two-piece conduit, each of which is slit open to ease installation and maintenance of wire and cable bundles. The interlocking construction is excellent for retrofitting projects. Polypropylene material is typically used in building construction, particularly where buried in concrete or plaster. Flexible, abrasion resistant and durable for a variety of applications.

Material	Polypropylene (PP)
Operating Temperature	-4°F to +194°F (-20°C to +90°C)
Flammability	EN IEC 61386
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	164.0 ft
Carton Qty.	1
Customs Number	3926909988

Inner Diameter (imperial)	0.55 "
Inner Diameter 2 (metric)	13.9 mm
Inside Bend Radius (imperial)	4.73 "
Inside Bend Radius (metric)	120 mm
Length (imperial)	164.0 ft
Length (metric)	50 m
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	21 mm
Outside Diameter (imperial)	0.84 "
Outside Diameter (metric)	21.2 mm

RoHS 