

TECHNICAL DATA SHEET

Part No. 169-23006
Article No. 169-23006
Type CTT-06 NSA935805-06



HellermannTyton's Polytetrafluoroethylene Convoluted Tubing provides an efficient method of routing and protecting wire harness assemblies while reducing the chance of installation damage. It also protects valuable hoses and cables. It is used in industries with demanding environments including aviation, aerospace, chemical, pharmaceutical, ship building, food processing and electrical.

Material	Polytetrafluoroethylene (PTFE)
Operating Temperature	-85°F to +500°F (-65°C to +260°C)
Flammability	FAR 25
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	164.04 ft
Carton Qty.	50
Customs Number	3926909988

Inner Diameter (imperial)	0.18 "
Inner Diameter 2 (metric)	4.6 mm
Length (imperial)	164.0 ft
Length (metric)	50.0 m
Nominal Diameter (imperial)	0.24 "
Nominal Diameter (metric)	6.0 mm
Outside Diameter (imperial)	0.32 "
Outside Diameter (metric)	8.10 mm

RoHS ✓