

TECHNICAL DATA SHEET

Part No. CTN1120
Article No. 169-60002
Type CTN1120



Convoluted tubing provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It also can serve to protect valuable wiring circuits. HellermannTyton's convoluted tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat or cold on cables and wires. Available in standard, bulk, and dispenser box packaging. Material is slit.

Material	Polyamide 6 (PA6)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 HB
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black with Gray Stripe (BKSTGY)
Pkg. Qty.	1000 ft
Carton Qty.	1000
Customs Number	3926909988

Inner Diameter (imperial)	1.647 "
Inner Diameter 2 (metric)	41.83 mm
Length (imperial)	1000.0 ft
Length (metric)	304.8 m
Nominal Diameter (imperial)	1.5 "
Nominal Diameter (metric)	38.1 mm
Outside Diameter (imperial)	1.947 "
Outside Diameter (metric)	49.45 mm
Wall Thickness (imperial)	0.006 "
Wall Thickness (metric)	0.152 mm

