

TECHNICAL DATA SHEET

Part No. 169-60118
Article No. 169-60118
Type CTPPFR380



HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The Polypropylene flame retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material.

Material	Polypropylene, flame retardant (PPFR)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Halogen Free	No
Use Conditions	For Indoor Use Only
Color	Black with Blue Stripe (BKSTBL)
Pkg. Qty.	1800 ft
Carton Qty.	1800
Customs Number	3926909988

Inner Diameter (imperial)	0.380 "
Inner Diameter 2 (metric)	9.65 mm
Length (imperial)	1800.0 ft
Length (metric)	548.6 m
Nominal Diameter (imperial)	0.38 "
Nominal Diameter (metric)	9.65 mm
Outside Diameter (imperial)	0.526 "
Outside Diameter (metric)	13.36 mm
Wall Thickness (imperial)	0.005 "
Wall Thickness (metric)	0.127 mm

