

# TECHNICAL DATA SHEET

**Part No.** 169-60119  
**Article No.** 169-60119  
**Type** CTPPFR580



HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The Polypropylene flame retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material.

<b>Inner Diameter (imperial)</b>	0.639 "
<b>Inner Diameter 2 (metric)</b>	16.23 mm
<b>Length (imperial)</b>	750.0 "
<b>Length (metric)</b>	228.6 mm
<b>Nominal Diameter (imperial)</b>	0.63 "
<b>Nominal Diameter (metric)</b>	16.00 mm
<b>Outside Diameter (imperial)</b>	0.837 "
<b>Outside Diameter (metric)</b>	21.26 mm
<b>Wall Thickness (imperial)</b>	0.005 "
<b>Wall Thickness (metric)</b>	0.127 mm

<b>Material</b>	Polypropylene, flame retardant (PPFR)
<b>Operating Temperature</b>	-40°F to +257°F (-40°C to +125°C)
<b>Halogen Free</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	Black with Blue Stripe (BKSTBL)
<b>Pkg. Qty.</b>	750 ft
<b>Carton Qty.</b>	750
<b>Customs Number</b>	3926909988

