

TECHNICAL DATA SHEET

Part No. 169-60128
Article No. 169-60128
Type CTPPFR1120



HellermannTyton's Convoluted Tubing, also known as split loom tubing, provides an efficient method of routing and protecting wire harness assemblies while reducing the chance of installation damage. With a split down the side where a wire harness can be inserted, installers can easily install convoluted tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The polypropylene flame-retardant material provides additional protection suitable for applications requiring a self-extinguishing material.

Material	Polypropylene, flame retardant (PPFR)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	self-extinguishing in 60 seconds
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Orange (OG), High Voltage (HV)
Pkg. Qty.	100
Carton Qty.	100
Customs Number	3926909988

Inner Diameter (imperial)	1.647 "
Inner Diameter 2 (metric)	41.83 mm
Length (imperial)	100.0 ft
Length (metric)	30.5 m
Nominal Diameter (imperial)	1-1/2 "
Nominal Diameter (metric)	38.1 mm
Outside Diameter (imperial)	1.947 "
Outside Diameter (metric)	49.45 mm
Wall Thickness (imperial)	0.006 "
Wall Thickness (metric)	0.152 mm

RoHS 