

TECHNICAL DATA SHEET

Part No. CTP1120STD
Article No. 169-60503
Type CTP1120



HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.

Material	Polyethylene (PE)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	not flame retardant
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	150 ft
Carton Qty.	150
Customs Number	3926909988

Inner Diameter (imperial)	1.647 "
Inner Diameter 2 (metric)	41.83 mm
Length (imperial)	150.0 ft
Length (metric)	45.7 m
Nominal Diameter (imperial)	1.5 "
Nominal Diameter (metric)	38.1 mm
Outside Diameter (imperial)	1.947 "
Outside Diameter (metric)	49.45 mm
Wall Thickness (imperial)	0.006 "
Wall Thickness (metric)	0.152 mm

RoHS 