

TECHNICAL DATA SHEET

Part No. 170-03006
Article No. 170-03006
Type BSPFR140



A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification. This fire extinguishing braided sleeving is ideal for electronic and high tech applications because of its lightweight and durable qualities.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 224 VW-1, Mil-202, FAR 25, FMVSS 302
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	200 ft
Carton Qty.	100
Customs Number	5808100000

Description	Standard-Size Reels
Max. Bundle Diameter (imperial)	0.44 "
Max. Bundle Diameter (metric)	11.1 mm
Min. Bundle Diameter (imperial)	0.13 "
Min. Bundle Diameter (metric)	3.2 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.4 mm
Reel Length (imperial)	200.0 ft
Reel Length (metric)	61.0 m

