

TECHNICAL DATA SHEET

Part No. 170-03035
Article No. 170-03035
Type BSPSC140



A versatile and economical general purpose sleeving that resists fraying when cut with ordinary scissors. For use in automotive, industrial and computer applications where the wires, cables and hoses being covered endure frequent handling. It is suited for situations where access to a hot knife is either impractical or impossible.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	25
Customs Number	5808100000

Max. Bundle Diameter (imperial)	0.44 "
Max. Bundle Diameter (metric)	11.1 mm
Min. Bundle Diameter (imperial)	0.16 "
Min. Bundle Diameter (metric)	4.0 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.4 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.5 m

HF✓

RoHS✓

