

TECHNICAL DATA SHEET

Part No. 170-03043
Article No. 170-03043
Type BSP340B



Designed to adjust and expand to irregular shapes, this general purpose sleeving is lightweight and offers a high tensile strength while still maintaining flexibility. This sleeving is an excellent choice for protecting wire and cable bundles from abrasion, chafing and heat degradation. Commonly used in electrical and industrial wire harnessing application where economy and durability are required for the protection of wires, cables, tubing, bundles and pneumatic hoses.

| | |
|------------------------------|-----------------------------------|
| Material | Polyester (PET) |
| Operating Temperature | -94°F to +257°F (-70°C to +125°C) |
| Melting Point | +482 °F (+250 °C) |
| Abrasion Resistance | Medium |
| Flammability | UL 94 V-0, FMVSS 302, FAR 25 |
| Halogen Free | Yes |
| UV Resistant | No |
| Use Conditions | For Indoor and Outdoor Use |
| Color | Black (BK) |
| Pkg. Qty. | 250 ft |
| Carton Qty. | 10 |
| Customs Number | 5808100000 |

| | |
|--|-----------------|
| Description | Bulk-Size Reels |
| Max. Bundle Diameter (imperial) | 1.25 " |
| Max. Bundle Diameter (metric) | 31.8 mm |
| Min. Bundle Diameter (imperial) | 0.5 " |
| Min. Bundle Diameter (metric) | 12.7 mm |
| Nominal Diameter (imperial) | 0.75 " |
| Nominal Diameter (metric) | 19.1 mm |
| Reel Length (imperial) | 250.0 ft |
| Reel Length (metric) | 76.2 m |

