

TECHNICAL DATA SHEET

Part No. 170-03064
Article No. 170-03064
Type BSHTTST10SR



High Temperature Aluminum Laminated Fiberglass Sleeve is a tubular shaped product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to reflect radiant heat away from the sensitive contents inside the tube.

Material	Aluminum (AL), Glass Fiber (GF)
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Melting Point	+2048 °F (1120 °C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Silver (SR)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	7019905150

Max. Bundle Diameter (imperial)	0.94 "
Max. Bundle Diameter (metric)	23.8 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.4 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.5 m
Wall Thickness (imperial)	0.025 "
Wall Thickness (metric)	0.64 mm

