

TECHNICAL DATA SHEET

Part No. 170-03114
Article No. 170-03114
Type BSHLR200



Halar self-extinguishing sleeving is used where flammability, high temperature endurance and low outgassing are the primary concern. This sleeving is made from strands of high temperature, flame resistant Halar monofilaments that are able to resist a wide range of corrosive chemicals and organic solvents. Its low flame spread and smoke generation properties make it the perfect option for use in technologically advanced applications, such as those in the automotive, aerospace and vital military markets.

Material	Ethylene Chlorotrifluoroethylene (E/CTFE)
Operating Temperature	-103°F to +302°F (-75°C to +150°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL VW-1, FAR 25
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50 ft
Carton Qty.	1
Customs Number	5808100000

Max. Bundle Diameter (imperial)	3.5 "
Max. Bundle Diameter (metric)	88.9 mm
Min. Bundle Diameter (imperial)	1.5 "
Min. Bundle Diameter (metric)	38.1 mm
Nominal Diameter (imperial)	2 "
Nominal Diameter (metric)	50.8 mm
Reel Length (imperial)	50.0 ft
Reel Length (metric)	15.2 m

