

TECHNICAL DATA SHEET

Part No. 170-03122
Article No. 170-03122
Type BSSCFR1120B



This protective sleeving is self-extinguishing and can be cut with sharp scissors instead of a hot knife for fray-resistant ends. Readily used in the automotive, audiovisual, industrial, wire, cable and computer industries where flame retardancy is required to reduce the likelihood of ignition and/or reduce the rate of flame spread. It is suited for situations where access to a hot knife is either impractical or impossible.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL VW-1, Mil-202
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250 ft
Carton Qty.	5
Customs Number	5808100000

Description	Bulk-Size Reels
Max. Bundle Diameter (imperial)	2 "
Max. Bundle Diameter (metric)	50.8 mm
Min. Bundle Diameter (imperial)	1.25 "
Min. Bundle Diameter (metric)	31.8 mm
Nominal Diameter (imperial)	1.5 "
Nominal Diameter (metric)	38.1 mm
Reel Length (imperial)	250.0 ft
Reel Length (metric)	76.2 m

HF ✓

LFH ✓

RoHS ✓

ASTM

NFPA 130

