

# TECHNICAL DATA SHEET

**Part No.** 170-03126  
**Article No.** 170-03126  
**Type** BSPSW120B



A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

|                              |                                   |
|------------------------------|-----------------------------------|
| <b>Material</b>              | Polyester (PET)                   |
| <b>Operating Temperature</b> | -94°F to +257°F (-70°C to +125°C) |
| <b>Melting Point</b>         | +482 °F (+250 °C)                 |
| <b>Abrasion Resistance</b>   | Medium                            |
| <b>Flammability</b>          | UL 94 V-0                         |
| <b>Halogen Free</b>          | Yes                               |
| <b>UV Resistant</b>          | Yes                               |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use        |
| <b>Color</b>                 | Black (BK)                        |
| <b>Pkg. Qty.</b>             | 150.0 ft                          |
| <b>Carton Qty.</b>           | 6                                 |
| <b>Customs Number</b>        | 5808100000                        |

| Description                            | Bulk-Size Reel |
|----------------------------------------|----------------|
| <b>Max. Bundle Diameter (imperial)</b> | 0.5 "          |
| <b>Max. Bundle Diameter (metric)</b>   | 12.7 mm        |
| <b>Min. Bundle Diameter (imperial)</b> | 0.1 "          |
| <b>Min. Bundle Diameter (metric)</b>   | 2.54 mm        |
| <b>Nominal Diameter (imperial)</b>     | 0.5 "          |
| <b>Nominal Diameter (metric)</b>       | 12.7 mm        |
| <b>Reel Length (imperial)</b>          | 150.0 ft       |
| <b>Reel Length (metric)</b>            | 45.7 m         |
| <b>Wall Thickness (imperial)</b>       | 0.025 "        |
| <b>Wall Thickness (metric)</b>         | 0.64 mm        |

