

TECHNICAL DATA SHEET

Part No. 170-03133
Article No. 170-03133
Type BSPSW140LB



A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	3000 ft
Carton Qty.	1
Customs Number	5808100000

Description	Bulk-Size Reel in Box
Max. Bundle Diameter (imperial)	0.25 "
Max. Bundle Diameter (metric)	6.4 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.4 mm
Reel Length (imperial)	3000.0 ft
Reel Length (metric)	914.4 m
Wall Thickness (imperial)	0.025 "
Wall Thickness (metric)	0.64 mm

