

TECHNICAL DATA SHEET

Part No. 170-03153
Article No. 170-03153
Type BSHKLPR120B



Flame retardant expandable braided sleeving with hook & loop strip for wrapping around cable assemblies. Color matched hook & loop closure provides an easy on and off installation, as well as convenient access for harness break-outs.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 224 VW-1
Halogen Free	Yes
UV Resistant	No
US MILSPEC	MIL-STD-202
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	5808100000

Max. Bundle Diameter (imperial)	0.5 "
Max. Bundle Diameter (metric)	12.7 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	0.5 "
Nominal Diameter (metric)	12.7 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.5 m
Wall Thickness (imperial)	0.025 "
Wall Thickness (metric)	0.635 mm

