

TECHNICAL DATA SHEET

Part No. 170-03159
Article No. 170-03159
Type BSNMX145B



A densely woven aramid fiber sleeving, this soft and flexible material is self extinguishing and can withstand temperatures reaching up to 662°F. Excellent for use in extremely harsh environments including those with exposure to direct flame, high temperatures, as well as Beta, Gamma and X-Ray radiation - in particular, military and aerospace wiring and harnessing applications.

Material	Polyaramid Polymetaphenylene Isophthalamide (PMPi)
Operating Temperature	-320°F to +662°F (-196 °C to +350 °C)
Abrasion Resistance	Low
Flammability	UL VW-1
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Green (GN)
Pkg. Qty.	100 ft
Carton Qty.	1
Customs Number	5808100000

Max. Bundle Diameter (imperial)	0.31 "
Max. Bundle Diameter (metric)	7.9 mm
Min. Bundle Diameter (imperial)	0.13 "
Min. Bundle Diameter (metric)	3.3 mm
Nominal Diameter (imperial)	0.25 "
Nominal Diameter (metric)	6.4 mm
Reel Length (imperial)	100.0 ft
Reel Length (metric)	30.5 m

HF✓

RoHS✓