

TECHNICAL DATA SHEET

Part No. 170-03178
Article No. 170-03178
Type BSP200B



Designed to adjust and expand to irregular shapes, this general purpose sleeving is lightweight and offers a high tensile strength while still maintaining flexibility. This sleeving is an excellent choice for protecting wire and cable bundles from abrasion, chafing and heat degradation. Commonly used in electrical and industrial wire harnessing application where economy and durability are required for the protection of wires, cables, tubing, bundles and pneumatic hoses.

Material	Polyester (PET)
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Melting Point	+482 °F (+250 °C)
Abrasion Resistance	Medium
Flammability	UL 94 V-0, FMVSS 302, FAR 25
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	200 ft
Carton Qty.	1
Customs Number	5808100000

Description	Bulk-Size Reels
Max. Bundle Diameter (imperial)	3.5 "
Max. Bundle Diameter (metric)	88.9 mm
Min. Bundle Diameter (imperial)	1.5 "
Min. Bundle Diameter (metric)	38.1 mm
Nominal Diameter (imperial)	2 "
Nominal Diameter (metric)	50.8 mm
Reel Length (imperial)	200.0 ft
Reel Length (metric)	61.0 m

