

TECHNICAL DATA SHEET

Part No. 170-03197
Article No. 170-03197
Type BSHTTSW112SB



Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks.

Material	Glass Fiber with Aluminium Foil (GF-AL)
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Melting Point	+2048 °F (1120 °C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Silver (SR)
Pkg. Qty.	4
Carton Qty.	1
Customs Number	7019905150

Max. Bundle Diameter (imperial)	1.45 "
Max. Bundle Diameter (metric)	36.8 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	1.5 "
Nominal Diameter (metric)	38.1 mm
Reel Length (imperial)	4.0 ft
Reel Length (metric)	1.22 m
Wall Thickness (imperial)	0.042 "
Wall Thickness (metric)	1.06 mm

