

TECHNICAL DATA SHEET

Part No. 170-03203
Article No. 170-03203
Type BSHDWV



Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.

Material	Polyamide 6 (PA6)
Operating Temperature	-49°F to +248°F (-45°C to +120°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50 ft
Carton Qty.	1
Customs Number	5806322000

Max. Bundle Diameter (imperial)	0.95 "
Max. Bundle Diameter (metric)	24.1 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25.4 mm
Reel Length (imperial)	50.0 ft
Reel Length (metric)	15.24 m
Wall Thickness (imperial)	.045 "
Wall Thickness (metric)	1.14 mm

HF ✓

RoHS ✓