TECHNICAL DATA SHEET

HellermannTyton

Part No. 170-03207
Article No. 170-03207
Type BSHDWV

Sleeving made of a tightly woven nylon fabric, slides onto hoses, cables and components to protect them from abrasion and environmental elements, including UV damage. Also protects surrounding surfaces from damage.

Material	Polyamide 6 (PA6)
Operating Temperature	-49°F to +248°F (-45°C to +120°C)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	25 ft
Carton Qty.	1
Customs Number	5806322000

Max. Bundle Diameter (imperial)	3 "
Max. Bundle Diameter (metric)	76.2 mm
Min. Bundle Diameter (imperial)	0.1 "
Min. Bundle Diameter (metric)	2.54 mm
Nominal Diameter (imperial)	3 "
Nominal Diameter (metric)	76.2 mm
Reel Length (imperial)	25.0 ft
Reel Length (metric)	7.62 m
Wall Thickness (imperial)	.045 "
Wall Thickness (metric)	1.14 mm

HF RoHS

Contact HellermannTyton for more information. Visit www.hellermann.tyton.com or call 800.537.1512
Disclaimer: The information in this datasheet is for informational purposes only.
Information is subject to change at any time without notice.

created on 2026-04-15