


TECHNICAL DATA SHEET

Part No. 170-22500
Article No. 170-22500
Type HEGPA6625



Helagaine Nylon Polyamide Expandable Braided Sleeve is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-76°F to +302°F (-60°C to +150°C)
Melting Point	+491 °F (+255 °C)
Abrasion Resistance	High
Flammability	UL 94 V-2, FMVSS 302
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	164.0 ft
Carton Qty.	1
Customs Number	5808100000

Max. Bundle Diameter (imperial)	1.1 "
Max. Bundle Diameter (metric)	28 mm
Min. Bundle Diameter (imperial)	0.71 "
Min. Bundle Diameter (metric)	18 mm
Nominal Diameter (imperial)	1 "
Nominal Diameter (metric)	25 mm
Reel Length (imperial)	164.0 ft
Reel Length (metric)	50.0 m

HF ✓

RoHS ✓