

TECHNICAL DATA SHEET

Part No. PR1M4
Article No. 181-00139
Type PR1



HellermannTyton panel rivets are one piece drive rivets that provide a fast, economic means of affixing wiring duct. The rivet is inserted into a 3/16" pre-punched hole and the pin is driven into the base, thereby expanding the rivet legs and locking the duct and sub-panel in place. The panel thickness (including the duct thickness) should be a maximum of 3/16".

Description

Panel Rivet, PA66, Natural, 1000/
bg

HF ✓

RoHS ✓

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	15000
Customs Number	3926909988