

# TECHNICAL DATA SHEET

**Part No.** 181-00211  
**Article No.** 181-00211  
**Type** SL1.5X3



Manufactured from the same PVC material as standard Pro-Duct colors, HellermannTyton also offers an intrinsic blue color option. The intrinsic blue color indicates that the wiring contained in the duct runs to intrinsically safe components in the control panel. Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

|                              |                                                 |
|------------------------------|-------------------------------------------------|
| <b>Material</b>              | Polyvinylchloride - rigid extrusion grade (PVC) |
| <b>Operating Temperature</b> | +122°F (+50°C)                                  |
| <b>Flammability</b>          | UL 94 V-0                                       |
| <b>Halogen Free</b>          | No                                              |
| <b>UV Resistant</b>          | No                                              |
| <b>Use Conditions</b>        | For Indoor Use Only                             |
| <b>Color</b>                 | Intrinsic Blue (IBU)                            |
| <b>Pkg. Qty.</b>             | 60.0 ft                                         |
| <b>Carton Qty.</b>           | 60.0 ft                                         |
| <b>Customs Number</b>        | 3925900000                                      |

|                                         |              |
|-----------------------------------------|--------------|
| <b>Fixation Method</b>                  | Non-Adhesive |
| <b>Height (imperial)</b>                | 3.07 "       |
| <b>Height (metric)</b>                  | 77.90 mm     |
| <b>Length (imperial)</b>                | 6.0 ft       |
| <b>Length (metric)</b>                  | 1.83 m       |
| <b>Mounting Hole Centers (imperial)</b> | 4.0 "        |
| <b>Mounting Hole Centers (metric)</b>   | 101.6 mm     |
| <b>Width (imperial)</b>                 | 1.5 "        |
| <b>Width (metric)</b>                   | 38.1 mm      |
| <b>Width 2 (imperial)</b>               | 1.5 "        |
| <b>Width 2 (metric)</b>                 | 38.1 mm      |
| <b>Width 3 (imperial)</b>               | 0.4 "        |
| <b>Width 3 (metric)</b>                 | 10.2 mm      |
| <b>Width 4 (imperial)</b>               | 1.0 "        |
| <b>Width 4 (metric)</b>                 | 25.4 mm      |
| <b>Width 5 (imperial)</b>               | 2.6 "        |
| <b>Width 5 (metric)</b>                 | 66.0 mm      |

