

# TECHNICAL DATA SHEET

**Part No.** 181-00262  
**Article No.** 181-00262  
**Type** TC2.5



HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

|                              |                         |
|------------------------------|-------------------------|
| <b>Material</b>              | Polyvinylchloride (PVC) |
| <b>Operating Temperature</b> | +122°F (+50°C)          |
| <b>Flammability</b>          | UL 94 V-0               |
| <b>Halogen Free</b>          | No                      |
| <b>UV Resistant</b>          | No                      |
| <b>Use Conditions</b>        | For Indoor Use Only     |
| <b>Color</b>                 | White (WH)              |
| <b>Pkg. Qty.</b>             | 120.0 ft                |
| <b>Carton Qty.</b>           | 120                     |
| <b>Customs Number</b>        | 3925900000              |

|                          |         |
|--------------------------|---------|
| <b>Height (imperial)</b> | 0.308 " |
| <b>Height (metric)</b>   | 7.82 mm |
| <b>Length (imperial)</b> | 6.0 ft  |
| <b>Length (metric)</b>   | 1.83 m  |
| <b>Width (imperial)</b>  | 2.5 "   |
| <b>Width (metric)</b>    | 63.5 mm |

