

TECHNICAL DATA SHEET

Part No. 181-00306
Article No. 181-00306
Type DV1.5



Solid-Wall Dividers can be securely mounted into all types of HellermannTyton wiring duct to separate high and low voltage, thus reducing interference. The dividers simply snap or slide into the specially designed mount, instantly creating multiple channels within a single duct size.

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	120.0 ft
Carton Qty.	120
Customs Number	3925900000

Description	Wiring Duct Divider, 1.5" High
Height (imperial)	1.40 "
Height (metric)	35.6 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Width (imperial)	0.75 "
Width (metric)	19.05 mm

RoHS ✓

