

TECHNICAL DATA SHEET

Part No. 181-00456
Article No. 181-00456
Type SD,75X,75



HellermannTyton Solid Wall Wiring Duct efficiently routes and protects wire. Solid wall wiring duct is designed for straight wire runs where breakouts are not required. Solid wall wiring duct is manufactured from high-impact, rigid PVC; comes in standard colors of white, gray and black; and is available in 6-foot lengths.

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	120.0 ft
Carton Qty.	120
Customs Number	3925900000

Height (imperial)	0.80 "
Height (metric)	20.3 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm
Width (imperial)	0.75 "
Width (metric)	19.1 mm
Width 2 (imperial)	1.0 "
Width 2 (metric)	25.4 mm

RoHS✓

