

TECHNICAL DATA SHEET

Part No. 181-00550
Article No. 181-00550
Type SL1.5X3



HellermannTyton Slotted Wall Wiring Duct features break-away fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and T's.

Material	Polyvinylchloride - rigid extrusion grade (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	60.0 ft
Carton Qty.	60
Customs Number	3925900000

Fixation Method	Non-Adhesive
Height (imperial)	3.07 "
Height (metric)	77.9 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm
Width (imperial)	1.5 "
Width (metric)	38.1 mm
Width 2 (imperial)	1.5 "
Width 2 (metric)	38.1 mm
Width 3 (imperial)	0.4 "
Width 3 (metric)	10.2 mm
Width 4 (imperial)	1.0 "
Width 4 (metric)	25.4 mm
Width 5 (imperial)	2.6 "
Width 5 (metric)	66.0 mm

