

TECHNICAL DATA SHEET

Part No. 181-00615
Article No. 181-00615
Type SLHD3X3



HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

| | |
|------------------------------|-------------------------|
| Material | Polyvinylchloride (PVC) |
| Operating Temperature | +122°F (+50°C) |
| Halogen Free | No |
| UV Resistant | No |
| Use Conditions | For Indoor Use Only |
| Color | Black (BK) |
| Pkg. Qty. | 60 ft |
| Carton Qty. | 60 |
| Customs Number | 3925900000 |

| | |
|---|--------------|
| Fixation Method | Non-Adhesive |
| Height (imperial) | 3.07 " |
| Height (metric) | 77.9 mm |
| Length (imperial) | 6.0 ft |
| Length (metric) | 1.83 m |
| Mounting Hole Centers (imperial) | 2.0 " |
| Mounting Hole Centers (metric) | 50.8 mm |
| Width (imperial) | 3.0 " |
| Width (metric) | 76.2 mm |
| Width 2 (imperial) | 3.0 " |
| Width 2 (metric) | 76.2 mm |
| Width 3 (imperial) | 0.16 " |
| Width 3 (metric) | 4.1 mm |
| Width 4 (imperial) | 0.4 " |
| Width 4 (metric) | 10.2 mm |
| Width 5 (imperial) | 2.6 " |
| Width 5 (metric) | 66.0 mm |

