

# TECHNICAL DATA SHEET

**Part No.** 181-05518  
**Article No.** 181-05518  
**Type** SD1X1



HellermannTyton Solid Wall Wiring Duct efficiently routes and protects wire. Solid wall wiring duct is designed for straight wire runs where breakouts are not required. Solid wall wiring duct is manufactured from high-impact, rigid PVC; comes in standard colors of white, gray and black; and is available in 6-foot lengths.

|                              |                         |
|------------------------------|-------------------------|
| <b>Material</b>              | Polyvinylchloride (PVC) |
| <b>Operating Temperature</b> | +122°F (+50°C)          |
| <b>Flammability</b>          | UL 94 V-0               |
| <b>Halogen Free</b>          | No                      |
| <b>UV Resistant</b>          | No                      |
| <b>Use Conditions</b>        | For Indoor Use Only     |
| <b>Color</b>                 | Intrinsic Blue (IBU)    |
| <b>Pkg. Qty.</b>             | 120.0 ft                |
| <b>Carton Qty.</b>           | 120.0 ft                |
| <b>Customs Number</b>        | 3925900000              |

|                                         |          |
|-----------------------------------------|----------|
| <b>Height (imperial)</b>                | 1.06 "   |
| <b>Height (metric)</b>                  | 26.90 mm |
| <b>Length (imperial)</b>                | 6.0 ft   |
| <b>Length (metric)</b>                  | 1.83 m   |
| <b>Mounting Hole Centers (imperial)</b> | 4.0 "    |
| <b>Mounting Hole Centers (metric)</b>   | 101.6 mm |
| <b>Width (imperial)</b>                 | 1.0 "    |
| <b>Width (metric)</b>                   | 25.4 mm  |
| <b>Width 2 (imperial)</b>               | 1.0 "    |
| <b>Width 2 (metric)</b>                 | 25.4 mm  |

RoHS ✓

