

TECHNICAL DATA SHEET

Part No. 181-15507
Article No. 181-15507
Type SL1.5X1.5



Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	30.0 ft
Carton Qty.	120.0 ft
Customs Number	3925900000

Fixation Method	Non-Adhesive
Height (imperial)	1.57 "
Height (metric)	39.9 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm
Width (imperial)	1.5 "
Width (metric)	38.1 mm
Width 2 (imperial)	1.5 "
Width 2 (metric)	38.1 mm
Width 3 (imperial)	0.4 "
Width 3 (metric)	10.2 mm
Width 4 (imperial)	1.0 "
Width 4 (metric)	25.4 mm
Width 5 (imperial)	1.2 "
Width 5 (metric)	30.5 mm

