

# TECHNICAL DATA SHEET

**Part No.** 181-21007  
**Article No.** 181-21007  
**Type** SL2X1



HellermannTyton Slotted Wall Wiring Duct features break-away fingers that provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and T's.

|                              |                         |
|------------------------------|-------------------------|
| <b>Material</b>              | Polyvinylchloride (PVC) |
| <b>Operating Temperature</b> | +122°F (+50°C)          |
| <b>Halogen Free</b>          | No                      |
| <b>UV Resistant</b>          | No                      |
| <b>Use Conditions</b>        | For Indoor Use Only     |
| <b>Color</b>                 | White (WH)              |
| <b>Pkg. Qty.</b>             | 120.0 ft                |
| <b>Carton Qty.</b>           | 120                     |
| <b>Customs Number</b>        | 3925900000              |

|                                         |              |
|-----------------------------------------|--------------|
| <b>Fixation Method</b>                  | Non-Adhesive |
| <b>Height (imperial)</b>                | 1.06 "       |
| <b>Height (metric)</b>                  | 26.9 mm      |
| <b>Length (imperial)</b>                | 6.0 ft       |
| <b>Length (metric)</b>                  | 1.83 m       |
| <b>Mounting Hole Centers (imperial)</b> | 4.0 "        |
| <b>Mounting Hole Centers (metric)</b>   | 101.6 mm     |
| <b>Width (imperial)</b>                 | 2.0 "        |
| <b>Width (metric)</b>                   | 50.8 mm      |
| <b>Width 2 (imperial)</b>               | 2.0 "        |
| <b>Width 2 (metric)</b>                 | 50.8 mm      |
| <b>Width 3 (imperial)</b>               | 0.4 "        |
| <b>Width 3 (metric)</b>                 | 10.2 mm      |
| <b>Width 4 (imperial)</b>               | 1.0 "        |
| <b>Width 4 (metric)</b>                 | 25.4 mm      |
| <b>Width 5 (imperial)</b>               | 0.75 "       |
| <b>Width 5 (metric)</b>                 | 19.1 mm      |

