

TECHNICAL DATA SHEET

Part No. 181-35002
Article No. 181-35002
Type SL3X5



Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Black (BK)
Pkg. Qty.	120.0 ft
Carton Qty.	120
Customs Number	3925900000

Fixation Method	Non-Adhesive
Height (imperial)	5.06 "
Height (metric)	128.5 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm
Width (imperial)	3.0 "
Width (metric)	76.2 mm
Width 2 (imperial)	3.0 "
Width 2 (metric)	76.2 mm
Width 3 (imperial)	0.4 "
Width 3 (metric)	10.2 mm
Width 4 (imperial)	1.0 "
Width 4 (metric)	25.4 mm
Width 5 (imperial)	4.6 "
Width 5 (metric)	116.8 mm

