

TECHNICAL DATA SHEET

Part No. 181-43004
Article No. 181-43004
Type SL4X3



Pro-Duct slotted wall wiring duct features break-away fingers which provide additional access for wire leads. Each section of the duct is provided with two score lines. The upper score line is used to break away fingers when a greater opening is required. The lower score line allows the sidewall to be smoothly cut for joints and Ts.

Material	Polyvinylchloride - rigid extrusion grade (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	120.0 ft
Carton Qty.	120
Customs Number	3925900000

Fixation Method	Non-Adhesive
Height (imperial)	3.07 "
Height (metric)	77.9 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Mounting Hole Centers (imperial)	4.0 "
Mounting Hole Centers (metric)	101.6 mm
Width (imperial)	4.0 "
Width (metric)	101.6 mm
Width 2 (imperial)	4.0 "
Width 2 (metric)	101.6 mm
Width 3 (imperial)	0.4 "
Width 3 (metric)	10.2 mm
Width 4 (imperial)	1.0 "
Width 4 (metric)	25.4 mm
Width 5 (imperial)	2.6 "
Width 5 (metric)	66.0 mm

