

TECHNICAL DATA SHEET

Part No. 181-91008
Article No. 181-91008
Type TC1



HellermannTyton's Pro-Duct wiring duct covers are sold separately and interchangeable among the 3 styles of duct (solid, slotted and high density). Manufactured from high impact, rigid PVC, Pro-Duct covers come in standard colors of white, gray and black. Wiring duct covers are available in 6 foot lengths.

Material	Polyvinylchloride (PVC)
Operating Temperature	+122°F (+50°C)
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	120.0 ft
Carton Qty.	120
Customs Number	3925900000

Description	Cover
Height (imperial)	0.290 "
Height (metric)	7.36 mm
Length (imperial)	6.0 ft
Length (metric)	1.83 m
Width (imperial)	1.0 "
Width (metric)	25.4 mm

RoHS 

