

TECHNICAL DATA SHEET

Part No. 183-11075
Article No. 183-11075
Type HTWD-HF-100X75




HellermannTyton HTWD-HF halogen-free ducts are used wherever there are high demands on personal or material safety, such as public transport, tunnels, escalators and data processing centers. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection. Base perforation according to DIN EN 50085.

Note: Halogen-free PC+ABS is not resistant to all oils and greases.

Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	52.49 ft
Carton Qty.	16.0 m
Customs Number	3925900000

Height (imperial)	2.95 "
Height (metric)	75.0 mm
Length (imperial)	6.56 ft
Length (metric)	2 m
Width (imperial)	3.94 "
Width (metric)	100 mm
Width 2 (imperial)	.20 "
Width 2 (metric)	5.0 mm
Width 3 (imperial)	.30 "
Width 3 (metric)	7.5 mm



EN 45545-2

