

TECHNICAL DATA SHEET

Part No. 183-28060
Article No. 183-28060
Type HTWD-HF-80X60



HelaDuct HTWD-HF wiring duct is used to route and protect wires in control panels and switching systems where there are high demands on personal or material safety in case of fire, such as in public transport, tunnels, data processing centers or public buildings. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection.

Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	65.62 ft
Carton Qty.	20.0 m
Customs Number	3925900000

Height (imperial)	2.36 "
Height (metric)	60.0 mm
Length (imperial)	6.56 ft
Length (metric)	2.0 m
Width (imperial)	3.15 "
Width (metric)	80.0 mm
Width 2 (imperial)	0.24 "
Width 2 (metric)	6.0 mm
Width 3 (imperial)	0.26 "
Width 3 (metric)	6.5 mm

HF ✓ RoHS ✓

EN 45545-2

UL C US