

# TECHNICAL DATA SHEET

**Part No.** 184-24007  
**Article No.** 184-24007  
**Type** SLHD2X4



HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.

<b>Material</b>	Polyvinylchloride (PVC)
<b>Operating Temperature</b>	+122°F (+50°C)
<b>Flammability</b>	UL 94 V-0
<b>Halogen Free</b>	No
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	White (WH)
<b>Pkg. Qty.</b>	60 ft
<b>Carton Qty.</b>	60
<b>Customs Number</b>	3925900000

<b>Fixation Method</b>	Non-Adhesive
<b>Height (imperial)</b>	4.07 "
<b>Height (metric)</b>	103.4 mm
<b>Length (imperial)</b>	6.0 ft
<b>Length (metric)</b>	1.83 m
<b>Mounting Hole Centers (imperial)</b>	2.0 "
<b>Mounting Hole Centers (metric)</b>	50.8 mm
<b>Width (imperial)</b>	2.0 "
<b>Width (metric)</b>	50.8 mm
<b>Width 2 (imperial)</b>	2.0 "
<b>Width 2 (metric)</b>	50.8 mm
<b>Width 3 (imperial)</b>	0.16 "
<b>Width 3 (metric)</b>	4.1 mm
<b>Width 4 (imperial)</b>	0.4 "
<b>Width 4 (metric)</b>	10.2 mm
<b>Width 5 (imperial)</b>	3.6 "
<b>Width 5 (metric)</b>	91.4 mm

