

TECHNICAL DATA SHEET

Part No. SNP210C2
Article No. 190-00101
Type SNP2



The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. These white polyacetal Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. Custom design and color options are available based upon application and volume requirements.

Material	Polyacetal (POM)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	White (WH)
Pkg. Qty.	100
Carton Qty.	8000
Customs Number	3926909988

Fixation Method	Plug-in mounting
Max. Bundle Diameter (imperial)	0.39 "
Max. Bundle Diameter (metric)	10.0 mm
Max. Width (imperial)	0.673 "
Max. Width (metric)	17.09 mm
Min. Bundle Diameter (imperial)	0.34 "
Min. Bundle Diameter (metric)	8.7 mm
Min. Width (imperial)	0.473 "
Min. Width (metric)	12.01 mm
Wall Thickness (imperial)	.067 "
Wall Thickness (metric)	1.7 mm

