

TECHNICAL DATA SHEET

Part No. SNP8GHS0M4
Article No. 190-00222
Type SNP8



The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. They are manufactured in black PA66 glass filled, impact modified, heat stabilized material. Custom design and color options are available based upon application and volume requirements.

Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	1000
Carton Qty.	6000
Customs Number	3926909988

Fixation Method	Plug-in mounting
Max. Bundle Diameter (imperial)	0.59 "
Max. Bundle Diameter (metric)	15.0 mm
Max. Width (imperial)	0.98 "
Max. Width (metric)	24.89 mm
Min. Bundle Diameter (imperial)	0.52 "
Min. Bundle Diameter (metric)	13.1 mm
Min. Width (imperial)	0.657 "
Min. Width (metric)	16.69 mm
Wall Thickness (imperial)	.07 "
Wall Thickness (metric)	1.818 mm

