

TECHNICAL DATA SHEET

Part No. 211-60007
Article No. 211-60007
Type H8P



HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	2000
Customs Number	3926909988

Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Mounting Hole Centers (imperial)	0.59 "
Mounting Hole Centers (metric)	15.0 mm
Mounting Hole Diameter (imperial)	0.17 "
Mounting Hole Diameter (metric)	4.2 mm
Width (imperial)	0.39 "
Width (metric)	10.0 mm

RoHS ✓